

## Coralene Blue HP-GS

A greenish blue disperse dye with excellent wet fastness properties suitable for bright shades; has good build up in continuous dyeing and is recommended for polyester / cotton blends.

### Suitability / Application:

#### Substrate:

Fiber / Yarn	-	●
Sewing threads	-	●
Piece dyeing	-	●
Micro fibers / fabric	-	●
P/C Blends - Exhaust, 2 bath	-	●
P/C Blends - Continuous	-	●
P/Elastane Blends	-	●
P/W Blends	-	○

#### Process:

##### Exhaust dyeing:

Low temperature with carrier - ○

HT, 135°C - ●

HT, Alkaline dyeing - ○

Continuous dyeing - ●

Printing - ●

##### Development method in printing:

Pressure Steaming - ●

HT Loop Steaming - ●

Discharge printing - ◻

### Exhaust Dyeing

1.160%



3.50% (1/1 SD)



5.25%



(Dyeing at 135°C for 45 min on polyester fabric at pH 4 adjusted with Levocol 4398)

### General properties:

C.T.Z.:	-	110 - 135°C
Leveling at 135°C:	-	Moderate
Migration:	-	Moderate
Recommended pH with buffer system :	-	4.0
Recommended auxiliary:	-	Levocol OA, 3 - 4 g/l
Dischargeability:(Zinc sulfoxylate formaldehyde)	-	Good
Sensitivity to metal (Fe)	-	Low
Stripping method	-	Reductive
Saturation value in HTHP exhaust dyeing (On 80D/36F polyester knit fabric)	-	5.50%

### Continuous dyeing

40.0 g/l on P/C cloth



### Shade change under artificial light:

D 65	Inc A	F 11 (TL 84)	F02 (CWF)	UL 35
Control	Tr R	R	R	R


### Cross staining on other components of blends in one bath dyeing:

Substrate	CA	PAN	PA	Cellulosic	Wool
Staining in dyebath	High	Moderate	High	Low	High
Staining after R.C.	High	Moderate	High	Low	Moderate


( Abbreviation: ● - Suitable, ○ - Not Suitable, ◐ - Limited suitability, ◻ - Not Recommended, R - Redder, G - Greener, Y - Yellower, B - Bluer)

## Coralene Blue HP-GS

### Product Performance:



(Dyeing at different dyebath temperature on polyester fabric at pH 4 adjusted with Levocol 4398)





(Exhaust dyeing different depth at 135°C temperature for 45 min on polyester fabric at pH 4 adjusted with Levocol 4398)

### Thermosol Application: (Pad - Dry - Thermosol)

40.0 gpl Coralene Blue HP-GS on P/C (67/33) fabric

### pH Sensitivity:

3.50% Coralene Blue HP-GS in exhaust dyeing



**Fastness Properties:** (Tested on 80D/36F 100% PET Knit, dyed by exhaust method)

- Light fastness (ISO 105 B02)
- Light fastness (AATCC 16, Option 3, 20 AFU)
- Sublimation fastness 1/1 SD (ISO 105 P01)

Shade change (Rating)		
1/6 SD	1/3 SD	1/1 SD
5	5-6	4-5
4.0	4.0	4.5

Temperature	180°C	190°C	200°C
C.O.S.	4-5	4-5	4-5
Staining on PET	4-5	4-5	4

## Coralene Blue HP-GS

**Fastness Properties:** ( Tested at 3.50% depth, on 80D/36F 100% PET Knit dyed by exhaust method and post set at 180<sup>o</sup>C for 30 Sec)

		Staining on						
		C.O.S.	Acetate	Cotton	Nylon	Polyester	Acrylic	Wool
● Perspiration Light fastness (ISO 105 B07)	Acid	4-5						
● Perspiration Light fastness (ISO 105 B07)	Alkaline	4-5						
● Wash fastness (ISO 105 C10 C, 60 <sup>o</sup> C)		4	4	4-5	4	4-5	4-5	4-5
● Wash fastness (ISO 105 C06, C2S, )		4	4	4-5	3-4	4	4-5	4-5
● Wash fastness (AATCC 61 Option 2A,49 <sup>o</sup> C)		4.0	4.0	4.0	3.5	4.0	4.5	4.5
● M&S C4A, 60 <sup>o</sup> C		4	4-5	4-5	4	4-5	4-5	4-5
● Adidas Wash fastness, 60 <sup>o</sup> C		4	3-4	4	3	4	4-5	4
● Dry cleaning fastness ( ISO 105 D01)		4	4-5	4-5	4-5	4-5	4-5	4-5
● Water fastness ( ISO 105 E01)		4-5	4	4-5	4	4-5	4-5	4-5
● Sea water fastness (ISO 105 E02)		4-5	4-5	4-5	4	4-5	4-5	4-5
● Chlorinated water fastness,(Adidas 5.06, 50 ppm)		4						
● Perspiration fastness (ISO 105 E04,Acid)		4-5	4	4-5	4	4-5	4-5	4-5
● Perspiration fastness (ISO 105 E04,Alkaline)		4-5	4	4-5	4	4-5	4-5	4-5
● Burnt gas fumes fastness (ISO 105 G02, 3 cycles)		4-5						
● Hypochlorite bleach fastness (ISO 105 N01)		4-5						
● Peroxide bleach fastness (ISO 105 N02)		4-5		4-5		4-5		
● Mercerization fastness (ISO 105 X04)		4-5		4-5				
● PVC migration (ISO 105 X10)		3-4	(Staining on PVC foil)					
● Crocking Fastness (ISO 105 X12, Dry/Wet)			4-5/4-5					
● Migration during storage (AATCC TM 163)		4.5	4.5	4.5	4.5	4.5	4.5	4.5
● Saliva fastness (DIN 53160)		5	(Staining on filter paper)					

**Fastness Properties:** (Tested at 6.30% depth, on 100% micro PET Knit (0.5 dpf) dyed by exhaust method and post set at 180<sup>o</sup>C for 30 Sec)

		Staining on						
		C.O.S.	Acetate	Cotton	Nylon	Polyester	Acrylic	Wool
● Light fastness (ISO 105 B02)		4						
● Wash fastness (ISO 105 C06, C2S, )		4	4	4	3-4	4	4-5	4-5
● Wash fastness (AATCC 61 Option 2A,49 <sup>o</sup> C)		4.0	4.0	4.0	3.5	4.0	4.5	4.5
● Water fastness ( ISO 105 E01)		4-5	4	4	4	4-5	4-5	4
● Crocking Fastness (ISO 105 X12, Dry/Wet)			4-5/4-5					

**Fastness Properties:** (Tested at 40.0 g/l depth, on P/C (67/33) blend twill fabric by continuous dyeing method and post set at 180<sup>o</sup>C for 30 Sec)

		Staining on						
		C.O.S.	Acetate	Cotton	Nylon	Polyester	Acrylic	Wool
● Wash fastness (ISO 105 C06, C2S, )		4	4-5	4-5	4-5	4-5	4-5	4-5
● Wash fastness (AATCC 61 Option 2A,49 <sup>o</sup> C)		4.0	4.0	4.5	3.5	4.0	4.5	4.5
● Water fastness ( ISO 105 E01)		4-5	4-5	4-5	4-5	4-5	4-5	4-5
● Crocking Fastness (ISO 105 X12, Dry/Wet)			4-5/4-5					

**Note:**

**Disclaimer:** This information is provided in good faith, to the best of our knowledge and without liabilities.



**Colourtex Industries Private Limited,**

91, Bhestan, Surat - 395023 (India)

Domestic: Tel.: +91 261 2897800/2897801

Export: Tel.: +91 261 2891427 /2897428

E mail: sales.surat@colourtex.co.in

E mail: ctx.export@colourtex.co.in